


Film, Film/Foil Polypropylene, Motor Run, C878, 8 uF, 5%, 450 V



General Information	
Dielectric:	Film/Foil Polypropylene
Style:	Can
Series:	C878
Description:	Aluminum Case, Plastic Cover, Spun Seal
Features:	Spun Seal, Safety Class P2, UL_94 V0 Disk
RoHS:	Yes
Lead:	Fast On (2+2)
Approvals:	UL, VDE, CQC, CSA (240VAC), UL_94 V0 Disk

Dimensions	
D	30mm +1mm
L	78mm +/-2mm

Specifications	
Capacitance:	8 uF
Capacitance Tolerance:	5%
Voltage AC:	450 VAC
Temperature Range:	-25/+85C
Rated Temperature:	85C
Max dVdt:	20 V

Packaging Specifications	
Mounting:	Bolt - M8x10
Packaging:	Bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.