

**KEMET Part Number: EFG(005)-240X240T0800**  
 (UFSEFG005AT080, EFG(005)240x240T0800)

Flex Suppressors, Commercial Grade, EFG



General Information	
Style:	Sheet
Brand:	TOKIN
Series:	EFG
Description:	Flex Suppressor Halogen Free Type
Features:	High Frequency Specifications
RoHS:	Yes
Approvals:	UL94 V-1
Environment:	Halogen Free, PVC Free, Lead Free

Dimensions	
Sheet Size	240x240mm
T	0.05mm +0.03/-0.005mm

Specifications	
Temperature Range:	-40/+105C
Magnetic Permeability:	20 TYP At 3MHz
Effective Frequency:	10 GHz MAX
Resistance:	0.1 MOhms MIN
Specific Gravity:	3 Atm TYP
Conductivity:	0.22 W/m K
Tensile Strength:	3.5 MPa MIN

Packaging Specifications	
Tape Description:	Without PET Tape (Txx00)
Tape Thickness:	.03mm