


Film, Metallized Polyester Stacked, Commercial Grade, F161, 0.1 uF, 10%, 100 V, 63 V, 85C, 2220, 4mm



Note: '()' correspond to the letters used in the product bulletin

General Information	
Dielectric:	Metallized Polyester Stacked
Style:	SMD Chip
Series:	F161
RoHS:	Yes
Approvals:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	This Capacitor Is Currently Under Development, Please Contact Kemet For Availability

Dimensions	
Chip Size	2220
L	5.7mm +/-0.2mm
W	5mm +/-0.2mm
T	4mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	2100

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC
Voltage AC:	63 V
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	0.8% 1kHz, 1.2% 10kHz, 2.5% 100kHz
Insulation Resistance:	1 GOhms
Max dVdt:	30 V