


Film, Metallized Polypropylene, Safety, F863, 6.8 uF, 10%, 310 V, 110C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm +0.3mm
H	44mm +0.1mm
T	24mm +0.3mm
S	37.5mm +/-0.4mm
LL	4mm +2mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Pizza
Packaging Quantity:	72

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	F863
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL, CQC

Specifications

Capacitance:	6.8 uF
Capacitance Tolerance:	10%
Voltage AC:	310 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.2% 1KHz
Insulation Resistance:	10 GOhms
Max dVdt:	100 V
Safety Class:	X2