


TOKIN Part Number: FC0H473ZFTBR24
(FC0H473ZF)

Supercapacitors, SMD Can, Commercial Grade, FC, 0.047 F, -20/+80%, 5.5 V, V-Chip



| Dimensions | |
|------------|-----------------|
| D | 10.5mm +/-0.5mm |
| L | 5.5mm MAX |
| W | 10.8mm +/-0.2mm |
| S | 5mm NOM |
| G | 0mm +0.3/-0.1mm |

| Packaging Specifications | |
|--------------------------|------------|
| Lead: | V-Chip |
| Packaging: | T&R, 380mm |

| General Information | |
|---------------------|--------------------------------------|
| Series: | FC |
| Description: | Surface Mount Double Layer Capacitor |
| Features: | Ultra Low ESR, High Power Pulse |
| RoHS: | Yes |

| Specifications | |
|------------------------|------------------------------------|
| Capacitance: | 0.047 F |
| Capacitance Tolerance: | -20/+80% |
| Voltage DC: | 5.5 VDC, 4.2 VDC (Holding Voltage) |
| Temperature Range: | -25/+70C |
| Rated Temperature: | 70C |
| Resistance: | 50000 mOhms (1kHz) |
| Current: | 0.071 mAmps (30min) |