


Supercapacitors, Radial Pin, Commercial Grade, FE, 1.5 F, -20/+80%, 5.5 V, Pin Leads, Lead Spacing = 20mm



Dimensions	
D	44.5mm +/-0.5mm
L	18.5mm MAX
S	20mm +/-0.5mm
LL Negative	6.4mm MIN
LL Positive	6.1mm MIN

Packaging Specifications	
Lead:	Pin Leads
Packaging:	Bulk

General Information	
Series:	FE
Description:	Radial Cylindrical Double Layer Capacitor
RoHS:	Yes
Miscellaneous:	DischargeValue = 2.1 F

Specifications	
Capacitance:	1.5 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC
Temperature Range:	-40/+70C
Rated Temperature:	70C
Resistance:	600 mOhms (1kHz)