


Supercapacitors, Radial Pin, Commercial Grade, FG, 0.47 F, -20/+80%, 5.5 V, Pin Leads, Lead Spacing = 5.08mm



Dimensions	
D	14.5mm +/-0.5mm
L	18mm MAX
S	5.08mm +/-0.5mm
LL Negative	2.7mm MIN
LL Positive	2.4mm MIN

Packaging Specifications	
Lead:	Pin Leads
Packaging:	Bulk

General Information	
Series:	FG
Description:	Radial Cylindrical Double Layer Capacitor
RoHS:	Yes
Miscellaneous:	DischargeValue = 0.6 F

Specifications	
Capacitance:	0.47 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70C
Resistance:	120000 mOhms (1kHz)