


Supercapacitors, Radial Pin, Commercial Grade, FGH, 1 F, -20/+80%, 5.5 V, Pin Leads, Lead Spacing = 7.62mm



Dimensions	
D	21.5mm +/-0.5mm
L	9.5mm MAX
S	7.62mm +/-0.5mm
LL Negative	3.3mm MIN
LL Positive	3mm MIN

Packaging Specifications	
Lead:	Pin Leads
Packaging:	Bulk

General Information	
Series:	FGH
Description:	Radial Cylindrical Double Layer Capacitor
RoHS:	Yes
Miscellaneous:	DischargeValue = 1 F

Specifications	
Capacitance:	1 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70C
Resistance:	35000 mOhms (1kHz)