


KEMET Part Number: SS11V-R08125-CH
(UAL11VR08125CH, SS11V/H-R08125-CH)

Commercial Grade, SS11V/H-CH, 0.0125 H



Dimensions

L	22mm +/-1mm
T	14.5mm +/-1mm
H	21.5mm +/-1mm
S	10mm +/-0.5mm
S1	13mm +/-0.5mm
LL	3.5mm +/-1mm
F	0.8mm NOM

Packaging Specifications

Weight:	9.8 g
----------------	-------

General Information

Style:	Through-Hole Choke
Series:	SS11V/H-CH
Description:	Common Mode Filter
RoHS:	Yes
Miscellaneous:	Inductance Measurement Condition: 1kHz 1V KC530

Specifications

Inductance:	12500 uH
Rated Temperature:	120C
Current:	0.8 Amps
Voltage AC:	250 VAC
DC Resistance:	740 mOhms
Insulation Resistance:	100 MOhms