


# BUTT DIN 46341




## Non-insulated

| Applicable Wire mm <sup>2</sup> | Part No. | Nominal Size DIN46341 | Dimensions mm (in.) |             |            | Tool No.   | Qty/box                |
|---------------------------------|----------|-----------------------|---------------------|-------------|------------|------------|------------------------|
|                                 |          |                       | ø d <sub>1</sub>    | l           | s          |            |                        |
| 0.1 to <0.5                     | C-0.5A   |                       | 1.2 (.047)          | 12.0 (.472) | 0.4 (.016) | WC-0510DIN | 2,000                  |
| 0.5 to 1                        | GSC-1    | 1                     | 1.6 (.063)          | 15.0 (.591) | 0.8 (.031) |            |                        |
| >1 to 2.5                       | GSC-2.5  | 2.5                   | 2.3 (.091)          | 15.0 (.591) | 0.8 (.031) |            | WC-0510DIN, WC-1016DIN |
| >2.5 to 6                       | GSC-6    | 6                     | 3.6 (.142)          | 15.0 (.591) | 1.0 (.039) |            |                        |
| >6 to 10                        | GSC-10   | 10                    | 4.5 (.177)          | 20.0 (.787) | 1.1 (.043) | WC-1016DIN | 500                    |
| >10 to 16                       | GSC-16   | 16                    | 5.8 (.228)          | 23.0 (.906) | 1.2 (.047) |            |                        |
| >16 to 25                       | GSC-25   | 25                    | 7.5 (.295)          | 25.0 (.984) | 1.5 (.059) | —          | 250                    |
| >25 to 35                       | GSC-35   | 35                    | 9.0 (.354)          | 27.0(1.063) | 1.6 (.063) |            | 200                    |
| >35 to 50                       | GSC-50   | 50                    | 11.0 (.433)         | 38.0(1.496) | 1.8 (.071) |            | 100                    |
| >50 to 70                       | GSC-70   | 70                    | 13.0 (.512)         | 42.0(1.654) | 2.0 (.079) |            | 100                    |
| >70 to 95                       | GSC-95   | 95                    | 15.0 (.591)         | 48.0(1.890) | 2.5 (.098) |            | 50                     |
| >95 to 120                      | GSC-120  | 120                   | 16.5 (.650)         | 52.0(2.047) | 3.0 (.118) |            | 50                     |
| >120 to 150                     | GSC-150  | 150                   | 19.0 (.748)         | 56.0(2.205) | 3.2 (.126) |            | 25                     |

Note:1) Contact J.S.T.(U.K.) Ltd for the above tools.

2) Delivery lead times may vary depending on the product. Contact JST for details.



## Vinyl-insulated

| Applicable Wire mm <sup>2</sup> | Part No.  | Nominal Size DIN46341 | Dimensions mm (in.) |                  |                |                |            | Color  | Tool No.   | Qty/box |
|---------------------------------|-----------|-----------------------|---------------------|------------------|----------------|----------------|------------|--------|------------|---------|
|                                 |           |                       | ø d <sub>1</sub>    | ø d <sub>2</sub> | l <sub>1</sub> | l <sub>2</sub> | s          |        |            |         |
| 0.5 to 1                        | FVGSC-1   | 1                     | 1.6 (.063)          | 3.4 (.134)       | 15.0 (.591)    | 25.0 (.984)    | 0.8 (.031) | Red    | WC-2210DIN | 1,000   |
| >1 to 2.5                       | FVGSC-2.5 | 2.5                   | 2.3 (.091)          | 4.3 (.169)       | 15.0 (.591)    | 25.0 (.984)    | 0.8 (.031) | Blue   | WC-2210DIN | 1,000   |
| >2.5 to 6                       | FVGSC-6   | 6                     | 3.6 (.142)          | 6.4 (.252)       | 15.0 (.591)    | 27.0(1.063)    | 1.0 (.039) | Yellow | WC-2210DIN | 500     |

Note:1) Contact J.S.T.(U.K.) Ltd for the above tools.

2) Delivery lead times may vary depending on the product. Contact JST for details.

## Nylon-insulated

| Applicable Wire mm <sup>2</sup> | Part No.  | Nominal Size DIN46341 | Dimensions mm (in.) |                  |                |                |            | Color  | Tool No.   | Qty/box |
|---------------------------------|-----------|-----------------------|---------------------|------------------|----------------|----------------|------------|--------|------------|---------|
|                                 |           |                       | ø d <sub>1</sub>    | ø d <sub>2</sub> | l <sub>1</sub> | l <sub>2</sub> | s          |        |            |         |
| 0.1 to <0.5                     | FNGSC-0.5 |                       | 1.2 (.047)          | 2.0 (.079)       | 12.0 (.472)    | 20.0 (.787)    | 0.4 (.016) | Yellow | —          | 2,000   |
| 0.5 to 1                        | FNGSC-1   | 1                     | 1.6 (.063)          | 3.2 (.126)       | 15.0 (.591)    | 25.0 (.984)    | 0.8 (.031) | Red    | WC-2210DIN | 1,000   |
| >1 to 2.5                       | FNGSC-2.5 | 2.5                   | 2.3 (.091)          | 3.8 (.150)       | 15.0 (.591)    | 25.0 (.984)    | 0.8 (.031) | Blue   | WC-2210DIN | 1,000   |
| >2.5 to 6                       | FNGSC-6   | 6                     | 3.6 (.142)          | 5.4 (.213)       | 15.0 (.591)    | 27.0(1.063)    | 1.0 (.039) | Yellow | WC-2210DIN | 500     |

Note:1) Contact J.S.T.(U.K.) Ltd for the above tools.

2) Delivery lead times may vary depending on the product. Contact JST for details.