






**User Manual**  
**Wall-Mount Enclosures M- type (Single & Double Door)**  
**GL66**




1 (1x)



2 (4x)




3 (4x)




4 (4x)




5 (1x)



6 (5x)



7



(8x)


(10x)

(12x)

(20x)

(24x)

8



(8x)


(10x)

(12x)


(20x)

(24x)


9









10 (5x)




11 (5x)
















M...P...GE




B-B






min 12mm ÷ max 25mm




10.5Nm  
93 in-lbs









  

CMFK  
CMFKSS  
CMTGFT  
GTBMTBKT




C-C







CMFK  
CMFKSS  
CMTGFT  
GTBMTBKT

22.5Nm  
200 in-lbs









CMFK  
CMFKSS  
CMTGFT  
GTBMTBKT





D-D










22.5Nm  
200 in-lbs









CMFK  
CMFKSS  
CMTGFT  
GTBMTBKT









F-F




MMK...E






min 12mm ÷ max 25mm



10.5Nm  
93 in-lbs



ADB.....E



4.3Nm  
38 in-lbs

