


KEMET Part Number: C192K104K1R5CA
(CK14BR104K)

Ceramic, Commercial Grade, MoldedStandard, 0.1 uF, 10%, 100 V, X7R



Dimensions

D	3.56mm +/-0.25mm
L	9.91mm +/-0.25mm
LL	38.1mm MIN
F	0.64mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	100

General Information

Series:	MoldedStandard
RoHS:	No
Termination:	Lead (SnPb)
Failure Rate:	N/A
Notes:	Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk

Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Insulation Resistance:	10 GOhms
Dielectric Strength:	250 V