



<b>General Features</b>	<b>Customer Model No. (Brand)</b>	C32229T2 Curve
	<b>Model No.</b>	
	<b>Panel (60Hz/120Hz/3D)</b>	ST3151A06-1(60Hz)
	<b>Destination Country</b>	UK&EU
	<b>Safety and Regulation</b>	CE,ROHS
	<b>Panel System</b>	31.5 inch LED Panel(Approx. 74cm)
	<b>Purpose</b>	TV/Monitor Optional
	<b>Aspect Ratio</b>	16:9
	<b>Max. Resolution</b>	1366 x 768
	<b>Contrast Ratio (Typical)</b>	3000:1(TYP) by panel
	<b>Brightness(TYP cd/m2)</b>	200nits(TYP) by panel
	<b>Display Area(mm)</b>	697.68 (H) x 392.256 (V)
	<b>Pixel Pitch (mm)</b>	0.17025 (H) x 0.51075 (V)
	<b>Display Colors</b>	16.7M
	<b>Viewing Angle( L/R/U/D )</b>	89/89/89/89(CR≥10)
	<b>HD Supported Definitions</b>	1080i/720P/576P/480P
	<b>Response Time(Tr+Tf /typ.)</b>	6.5ms
	<b>AC Switch</b>	N/A
	<b>Cabinet Color</b>	Piano Black
	<b>Tilt Angle (up and down movement)</b>	N/A
<b>Swivel Angle (left and right movement)</b>	N/A	
<b>Wall Mounting Support(Screw Size)</b>	VESA,200 x 200mm(M4 x 12)	

<b>Reception</b>	<b>TV Solution</b>	Mstar3463
	<b>TV System</b>	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	<b>TV Band</b>	ATV 49MHz - 863MHz DTV VHF (174MHz - 230MHz) UHF (474MHz - 862MHz)
	<b>5V from Antenna</b>	N/A
	<b>NTSC Playback</b>	N/A
	<b>Digital Comb Filter</b>	3D
	<b>De-interlace Image Enhancement</b>	N/A
	<b>Tuning System</b>	FST
	<b>Clock / Time Display</b>	N/A
	<b>CI PLUS</b>	N/A
	<b>Number of channel for storing</b>	100 Analog / 400 Digital
<b>Sound</b>	<b>Bass</b>	YES
	<b>Treble</b>	YES
	<b>Balance</b>	YES
	<b>Sound Mode</b>	Standard / Music /Movie / Sports /User
	<b>Stereo System</b>	NICAM/A2
	<b>Audio Output</b>	2*6W
	<b>Dolby</b>	N/A
	<b>SRS</b>	N/A
<b>Connectors Jack</b>	<b>RF Antenna</b>	1
	<b>HDMI</b>	YES x 3
	<b>CVBS</b>	YES x 1
	<b>PC In</b>	D-sub 15Pin x 1
	<b>Audio In</b>	PC audio x 1(3.5 φ Mini Jack) CVBS Audio x 1
	<b>Scart</b>	YES x 1
	<b>YPbPr</b>	YES x 1
	<b>Digital Audio Out</b>	YES x 1
	<b>Earphone Out</b>	YESx 1 (3.5 φ Mini Jack)
	<b>USB</b>	YES x 1( Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov,*.mkv,*.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	<b>CI</b>	YES x 1
<b>RCA</b>	N/A	
<b>Other Features</b>	<b>APS</b>	ATV, DVBT, DVBC storage in capture order
	<b>OSD Language</b>	English / French / German / Italian/Spanish/Portuguese
	<b>Teletext</b>	1000pages
	<b>EPG (Electronic Program Guide)</b>	7 days (not 7 days from satellite transmissions)
	<b>Automatic Tuning</b>	YES
	<b>Sleep Timer</b>	YES (240min)
	<b>Noise Reduction</b>	YES
	<b>Color Temperature Adjustment</b>	YES
	<b>Picture Mode</b>	Standard /Dynamic/Mild /User
	<b>Home Mode</b>	YES
	<b>Sleep Mode</b>	YES
<b>Hotel Mode</b>	YES	

<b>Power</b>	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	32W
	Max power Consumption	<60W
	Standby Power Consumption	0.4W
	Energy Efficiency Class	A
<b>Accessories</b>	USER'S Manual	ENGLISH
	Remote Control	YES x 1
	Power Cable	YES x 1
	Adapter	N/A
	Adapter Cables	N/A
	Warranty	YES
	Battery	1.5V(AAA)+2
<b>Dimension</b>	Unit Dimension With Stand (W x H x D mm)	733*469*153
	Unit Dimension Without Stand (W x H x D mm)	733*431*103
	Weight of unit (kg)	4.4 kg
	Carton Dimension With Stand Assembled (W x H x D) mm	/
	Carton Dimension Without Stand Assembled (W x H x D) mm	/
	Weight of gift box with content(kg)	
	Dimensions of mastercarton (W x H x D mm)	/
	Weight of mastercarton with content(Kg)	/
	Weight of carton/paper(Kg)	/
	Weight of styrofoam(Kg)	/
	Container Loading QTY (20GP/40GP/40HQ) (pcs)	/

Please note: the panels parameters listed in the spec are only for reference