

Brand Name:	Acer
DVI:	Yes
DisplayPort:	Yes
Environmentally Friendly:	Yes
Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Number of USB 2.0 Ports:	6
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i5-6400
Processor Speed:	2.70 GHz
Processor Type:	Core i5
Product Family:	Veriton X4640G
Product Type:	Desktop Computer
Standard Memory:	8 GB
Total Hard Drive Capacity:	1 TB
Total Number of USB Ports:	10
VGA:	Yes

Display & Graphics

Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
TV Card:	No

General Information

Brand Name:	Acer
Manufacturer Part Number:	DT.VMWEK.005
Manufacturer Website Address:	http://www.acer.co.uk
Manufacturer:	Acer, Inc
Product Line:	Veriton
Product Name:	Veriton X4640G Desktop Computer
Product Series:	X4640G
Product Type:	Desktop Computer

I/O Expansions

Number of M.2 Interfaces:	1
Number of PCI Express x1 Slots:	1
Number of PCI Express x16 Slots:	1
Number of Total Expansion Slots:	2

Input Devices

Keyboard Type:	Physical Keyboard
Keyboard:	Yes
Pointing Device Type:	Mouse

Interfaces/Ports

Audio Line In:	Yes
Audio Line Out:	Yes
DVI:	Yes
DisplayPort:	Yes
Modem (RJ-11):	No
Network (RJ-45):	Yes
Number of USB 2.0 Ports:	6
Number of USB 3.1 Gen 1 Ports:	4
Total Number of USB Ports:	10
VGA:	Yes

Memory

Maximum Memory:	64 GB
Memory Card Reader:	No
Memory Standard:	DDR4-2133/PC4-17000

Memory Technology: DDR4 SDRAM
Standard Memory: 8 GB

Miscellaneous

Certifications & Standards:

- DMI
- GS
- PC2001
- Citrix ready
- BSMI
- VCCI
- CE
- FCC
- CB

Environmental Certification: RoHS
Environmentally Friendly: Yes
Features: Security Slot
Package Contents:

- Veriton X4640G Desktop Computer
- USB Keyboard
- USB Mouse

Network & Communication

Ethernet Technology: Gigabit Ethernet
Modem: No

Physical Characteristics

Depth: 392.1 mm
Height: 267 mm
Width: 100 mm

Power Description

Maximum Power Supply Wattage: 220 W

Processor & Chipset

64-bit Processing: Yes
Cache: 6 MB
Chipset Manufacturer: Intel
Chipset Model: B150
Direct Media Interface: 8 GT/s
Maximum Turbo Speed: 3.30 GHz
Number of Processors Installed: 1
Number of Processors Supported: 1
Processor Core: Quad-core (4 Core)
Processor Manufacturer: Intel
Processor Model: i5-6400
Processor Speed: 2.70 GHz
Processor Type: Core i5

Software

Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro
Software Included: Microsoft Office trial

Storage

Hard Drive Configuration: 1 x 1 TB
Hard Drive Interface: Serial ATA/300
Hard Drive RPM: 7200
Number of Hard Drives: 1
Optical Drive Type: DVD-Writer
Optical Media Supported: DVD-RAM/±R/±RW
Total Hard Drive Capacity: 1 TB