


UL SOLID UL PC 1919 13 G



Sample photo

Order symbol: UL PC 1919 13 G
Product nbr: 5320359
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074037442
EI. number:
Finland:
Electric No. 8212033016
Denmark:
Electric No. Italy: 7401010U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

| Dimensions: | | | | Rating: |
|-------------------------------------|----------------------|--------|-----|--|
| Length | Width | Height | | |
| mm: | 188 | 188 | 130 | Ingress Protection (EN 60529): IP66/IP67 |
| inch: | 7.4 | 7.4 | 5.1 | Impact Resistance (EN 62262): IK08 |
| Materials: | | | | Electrical insulation: Totally insulated |
| Material: | Polycarbonate | | | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Base colour: | RAL 7035 -light grey | | | UV resistance: UL 508 |
| Cover screws material: | Polyamide | | | Flammability Rating: UL 746C 5" |
| Cover colour: | RAL 7035 -light grey | | | UL Type: |
| Cover screws colour: | Grey | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| Gasket material: | Polyurethane | | | Certificates: |
| Temperatures: | | | | Underwriters Laboratories |
| Temperature °C (short term): | -40 ... 120 °C | | | SGS Fimko |
| Temperature °C (continuous): | -40 ... 80 °C | | | UL Canada |
| Temperature °F (short term): | -40 ... 250 °F | | | Gost R |
| Temperature °F (continuous): | -40 ... 175 °F | | | |

