

UL MNX UL PC 125/60 HT



Sample photo

Order symbol:	UL PC 125/60 HT	EAN:	6418074014597
Product nbr:	6411907	EI. number:	
Description:	UL Enclosure, PC	Finland:	
Remarks:	Smoked transparent cover	Electric No. Denmark:	8212030271
		Electric No. Italy:	7352055U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
	Length	Width	Height	
mm:	130	130	60	Ingress Protection (EN 60529): IP66/IP67
inch:	5.1	5.1	2.4	Impact Resistance (EN 62262): IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:	Polyamide			Flammability Rating: UL 746C 5"
Cover colour:	Smoked grey			UL Type:
Cover screws colour:	Black			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	TPE			Certificates:
Temperatures:				Germanischer Lloyd (GL)
Temperature °C (short term):	-40 ... 120 °C			Underwriters Laboratories
Temperature °C (continuous):	-40 ... 80 °C			SGS Fimko
Temperature °F (short term):	-40 ... 250 °F			UL Canada
Temperature °F (continuous):	-40 ... 175 °F			Gost R

