

**UL PICCOLO UL PC M 95 G**



Sample photo

**Order symbol:** UL PC M 95 G  
**Product nbr:** 8714318  
**Description:** UL Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074038999  
**EI. number:**  
**Finland:**  
**Electric No.:** 8212031199  
**Denmark:**  
**Electric No. Italy:** 7201060U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	230	140	95	Ingress Protection (EN 60529): IP66/IP67
inch:	9.1	5.5	3.7	Impact Resistance (EN 62262): IK08
Materials:				Electrical insulation: Totally insulated
<b>Material:</b>	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7035 -light grey			UV resistance: UL 508
<b>Cover screws material:</b>	Polyamide			Flammability Rating: UL 746C 5"
<b>Cover colour:</b>	RAL 7035 -light grey			UL Type:
<b>Cover screws colour:</b>	Grey			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>	Polyurethane			Certificates:
Temperatures:				Germanischer Lloyd (GL)
<b>Temperature °C (short term):</b>	-40 ... 120 °C			Underwriters Laboratories
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			SGS Fimko
<b>Temperature °F (short term):</b>	-40 ... 250 °F			UL Canada
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Gost R

PICCOLO 230x140x95-125

