

M9A26946

Multi 9 - shunt trip release with OC - MX + OF -
110/415 V AC - 110/130 V DC

Product availability : Stock - Normally stocked in distribution facility



Main

Range	Multi 9
Product or component type	Shunt trip release with OC contact
Device short name	MX + OF
Signal contacts composition	1 C/O
[Ie] rated operational current	3 A at 415 V AC 6 A at <= 240 V AC
[Uc] control circuit voltage	110...130 V DC 110...415 V AC 50/60 Hz
9 mm pitches	2

Complementary

Range compatibility	Multi 9: Multi 9 C60 C60BP Multi 9: Multi 9 C60 C60BPR Multi 9: Multi 9 C60 C60SP Multi 9: Multi 9 GFP GFP Multi 9: Multi 9 C60H-DC C60H-DC
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Product weight	0.14 lb(US) (0.065 kg)
Connections - terminals	Clamp terminal bottom 1 cable(s) 0 in ² (2.5 mm ²) rigid (AWG 14) Clamp terminal bottom 2 cable(s) 0 in ² (1.5 mm ²) rigid (AWG 16)
Wire stripping length	0.35 in (9 mm) bottom
Tightening torque	8.85 lbf.in (1 N.m) bottom

Environment

Standards	EN/IEC 60947-1
Product certifications	CCC CSA UL UR PCT
Pollution degree	3
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	00785901760689
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16
Returnability	Y
Country of origin	BE