

Product availability : Stock - Normally stocked in distribution facility



### Main

|                              |                         |
|------------------------------|-------------------------|
| Range                        | Multi 9                 |
| Product or component type    | Undervoltage release    |
| Device short name            | MNs                     |
| [Uc] control circuit voltage | 220...240 V AC 50/60 Hz |
| Control type                 | Delayed                 |
| 9 mm pitches                 | 2                       |

### Complementary

|                         |  |
|-------------------------|--|
| Range compatibility     | Multi 9: Multi 9 C60 C60BP<br>Multi 9: Multi 9 C60 C60BPR<br>Multi 9: Multi 9 C60 C60SP<br>Multi 9: Multi 9 GFP GFP<br>Multi 9: Multi 9 C60H-DC C60H-DC                              |
| Local signalling        | Action indicator   |
| Mounting mode           | Fixed  |
| Mounting support        | DIN rail   |
| Height                  | 3.25 in (82.5 mm)  |
| Width                   | 0.71 in (18 mm)  |
| Depth                   | 2.68 in (68 mm)  |
| Product weight          | 0.15 lb(US) (0.066 kg)   |
| Connections - terminals | Clamp terminal bottom 1 cable(s) 0 in <sup>2</sup> (2.5 mm <sup>2</sup> ) rigid (AWG 14)<br>Clamp terminal bottom 2 cable(s) 0 in <sup>2</sup> (1.5 mm <sup>2</sup> ) rigid (AWG 16) |
| Wire stripping length   | 0.35 in (9 mm) bottom  |
| Tightening torque       | 8.85 lbf.in (1 N.m) bottom   |

### Environment

|           |                              |
|-----------|------------------------------|
| Standards | EN 60947-2<br>EN/IEC 60947-1 |
|-----------|------------------------------|

|                                       |                            |
|---------------------------------------|----------------------------|
| Product certifications                | CSA<br>UL<br>UR<br>PCT     |
| Pollution degree                      | 3                          |
| Ambient air temperature for operation | -13...122 °F (-25...50 °C) |
| Ambient air temperature for storage   | -40...185 °F (-40...85 °C) |

### Ordering and shipping details

|                       |                                  |
|-----------------------|----------------------------------|
| Category              | 00948 - M9 GEN 2 CB UL1077 / IEC |
| Discount Schedule     | DE2                              |
| GTIN                  | 00785901761341                   |
| Nbr. of units in pkg. | 1                                |
| Package weight(Lbs)   | 0.17000000000000001              |
| Returnability         | Y                                |
| Country of origin     | BE                               |