

Product availability : Stock - Normally stocked in distribution facility



Main

Range	Multi 9
Product or component type	Undervoltage release
Device short name	MNx
[Uc] control circuit voltage	400 V AC 50/60 Hz
Control type	With external feeding
9 mm pitches	2

Complementary

Range compatibility	Multi 9: Multi 9 C60 C60BP Multi 9: Multi 9 C60 C60BPR Multi 9: Multi 9 C60 C60SP Multi 9: Multi 9 GFP GFP Multi 9: Multi 9 C60H-DC C60H-DC
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Product weight	0.16 lb(US) (0.073 kg)
Connections - terminals	Clamp terminal bottom 1 cable(s) 0 in ² (2.5 mm ²) rigid (AWG 14) Clamp terminal bottom 2 cable(s) 0 in ² (1.5 mm ²) rigid (AWG 16)
Wire stripping length	0.35 in (9 mm) bottom
Tightening torque	8.85 lbf.in (1 N.m) bottom

Environment

Standards	EN/IEC 60947-1
Product certifications	CSA UL UR

PCT

Pollution degree	3
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	00785901761747
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17999999999999999
Returnability	Y
Country of origin	BE