

Product availability : Stock - Normally stocked in distribution facility



### Main

Range	Multi 9
Product or component type	Shunt trip release
Device short name	MX
[Uc] control circuit voltage	12...24 V AC 50/60 Hz 12...24 V DC
9 mm pitches	2

### Complementary

Range compatibility	Multi 9: Multi 9 C60 C60BP Multi 9: Multi 9 C60 C60BPR Multi 9: Multi 9 C60 C60SP Multi 9: Multi 9 GFP GFP Multi 9: Multi 9 C60H-DC C60H-DC
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Product weight	0.13 lb(US) (0.06 kg)
Connections - terminals	Clamp terminal bottom 1 cable(s) 0 in <sup>2</sup> (2.5 mm <sup>2</sup> ) rigid (AWG 14) Clamp terminal bottom 2 cable(s) 0 in <sup>2</sup> (1.5 mm <sup>2</sup> ) rigid (AWG 16)
Wire stripping length	0.35 in (9 mm) bottom
Tightening torque	8.85 lbf.in (1 N.m) bottom

### Environment

Standards	EN/IEC 60947-1
Product certifications	CSA

UL  
UR  
PCT

Pollution degree	3
Tropicalisation	2 conforming to EN/IEC 60947-1
Relative humidity	95 % at 131 °F (55 °C)
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

### Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	00785901758747
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16
Returnability	Y
Country of origin	BE