


z10 720p HD WiFi Camera



Features

-  Vivid HD Image
-  IR Night Vision
-  Two Way Audio
-  Simple Setup: Access Point WiFi Pairing Mode

Specification

Video	Image Sensor	1/4" CMOS
	Resolution	1280x720
	Pixels	1.0MP
	Compression	H.264
	Frame Rate	25fps max
	Bit Rate	64Kbps~8Mbps
	Minimum Illumination	0.5 Lux
Lens	Lens Mount	M12
	Lens	3.6mm
	View Angle	71°
	Focus	Fixed
Function	Motion Detection	Video Motion Detection
	Exposure Control	Auto
	Gain Control	Auto
	White Balance	Auto
	Day & Night	Auto IR Cut Filter, Color to Black
	Video Adjust	Contrast, Brightness, Saturation, Sharpness
	Two Way Audio	
	Local Storage	Micro SD Card - 64G max
Interface	Audio Input	1x Built-in MIC
	Audio Output	1x Built-in Speaker
	Reset Button	Factory Defaults + Reboot
Network	Wireless	IEEE 802.11b/g/n
	Dual Stream	Dual H264 Streams/6 simultaneous users Resolutions: 1024x720, 512x288
	Protocol	HTTP,TCP/IP,ICMP,UDP,SMTP,DHCP,DNS
General	Infrared Lamp	10 LEDs
	IR distance (m)	10m
	Temperature	-20°C~55°C
	Humidity	10%~90%
	Power Supply	DC 5V
	Power	3.2W max
	Material	White PVC
Size (WxHxD)(mm)	78x120x90	
Weight (g)	130	
Installation	Wall/Ceil/Desk Mounting	