



6 outlet surge protector, with 250J, lighted breaker switch and 3ft cord

SPECIFICATION		MODEL NUMBER:	28-8470
AC RATING		125V/15A/1875W/60HZ	
HOUSING		PLASTIC	
COLOR		LIGHT GRAY	
SOCKETS (TOTAL)		6	
TRANSFORMER SOCKETS (BLOCKSPACE)		x	
SLIDE SAFETY COVER		x	
POWER CABLE LENGTH (EXPOSED)		3ft	
POWER CABLE JACKET MATERIAL		PVC	
POWER CABLE CONDUCTOR SPECIFICATION		x	
AC PLUG STYLE		NEMA 15P	
OVERLOAD PROTECTION		15A	
SWITCH		LIGHTED BREAKER SWITCH	
GAS TUBES FOR GROUND CONNECTION		x	
POWER SAFETY SHUT DOWN PROTECTION		x	
THERMAL PROTECTION FOR MOVs		1 x 5A THERMAL FUSES	
MOV	L-N	1x14mm 201KD@250J+	
	L-G	x	
	N-G	x	
AC CIRCUIT TOTAL JOULES:		250J	
MAX. SPIKE CURRENT (TOTAL)		4500A	
MAX. SPIKE VOLTAGE		6000V	
MOV CLAMPING VOLTAGE		500V (L-N)	
RESPONSE TIME <1 NANOSECOND		YES	
SURGE INDICATOR (Protected)		x	
POWER ON INDICATOR (SLAVES) OR WIRE FAULT		x	
USB Charger		X	
Start Slaves Power			
Standby Power			
F-TYPE (USA) COAXIAL CABLE (1 x 6')		X	
PACKAGING STYLE		color box	
WARRANTY SHEET			
BAR CODE LABEL ON CASE PACK (2PCS)			
CASEPACK QUANTITY		36 PCS.	
STANDARD EXPORT CARTON DESIGN		YES	
CERTIFICATIONS US STANDARD		UL/cUL	
<b>REGULATORY STANDARDS:</b>			
ITEM	STANDARDS		
Products:			
Socket-Outlet Products:	UL 498A		
Electromagnetic Compatibility:	UL 1449 3rd edition		
	UL 60950		
	UL1283		