


## Intensifier H® Series Indoor/Outdoor Bullet Camera

See Color In Almost Complete Darkness Without IR LEDs

<b>HTINTB8H</b>	2.8 -12mm auto iris varifocal lens, dark grey housing
<b>HTINTB8HW</b>	2.8 -12mm auto iris varifocal lens, white housing
<b>HTINTB9H</b>	5-50mm auto iris varifocal lens, dark grey housing
<b>HTINTB9HW</b>	5-50mm auto iris varifocal lens, white housing
<b>HTINTB10H</b>	9-22mm auto iris varifocal lens, dark grey housing
<b>HTINTB10HW</b>	9-22mm auto iris varifocal lens, white housing

### Features

- 1/3" Sony Super HAD™ CCD
- 700 lines of color resolution
- Amplify existing light with no distance limitations
- No problems caused by objects that reflect or absorb IR light sources
- Minimum illumination 0.00002 lux (Intensify @ 512x)
- Now with presets: Outdoor, Indoor, Elevator, Lobby, Hallway & Dark
- 12VDC / 24VAC dual voltage operation
- Full OSD operation
- External controls for zoom & focus
- S/N Ratio more than 52dB (weight on)
- EZ mount system simplifies installation
- Relay outputs for motion detection
- Weather resistant operation
- IP66 compliant
- Anti-moisture glass and circuitry eliminates fog or condensation under any weather condition
- 5 year warranty



### Specifications

Image Sensor .....	1/3" Sony Super HAD™ CCD	White Balance .....	ATW / Outdoor / Indoor / Manual / AWC (1,700°K – 11,000°K)
Resolution .....	700 TV lines	Intensify .....	Auto / Off (selectable 2x – 512x)
Minimum Illumination .....	CDS off: 0.15 lux CDS on: 0.00002 lux	Motion Detection .....	On / Off (8 programmable zones)
Effective Pixels .....	976 (H) x 494 (V)	Privacy Masking .....	On / Off (12 programmable zones)
Total Pixels .....	1020 (H) x 508 (V)	Speco DNR .....	On / Off (level adjustable)
TV System .....	NTSC	Digital Zoom .....	On / Off (1x - 16x)
Scanning Frequency .....	15.734kHz (H) & 59.94Hz (V)	DIS .....	On / Off
Scanning System .....	2:1 interlace	Sharpness .....	On / Off (level adjustable)
Synchronization .....	Internal	Flip / Mirror .....	On / Off
S/N Ratio .....	More than 52dB	Power Consumption .....	12VDC, 400mA / 24VAC, 170mA
Video Output .....	CVBS: 1.0Vp-p / 75 ohms	Power Supply .....	12VDC / 24VAC dual voltage operation (power supply not included)
Electronic Shutter Speed .....	1/60 sec. – 1/120,000 sec.	Operating Temperature .....	-4° F – 140° F
OSD .....	Available	Dimensions .....	3.46" (W) x 4.01" (H) x 11.02" (L)
DWDR .....	On / Off (level adjustable)	Weight .....	3 lbs.
Backlight Compensation .....	BLC / HLC / Off		
Day/Night .....	Color / BW / Auto / Ext		
AGC .....	High / Low / Off		

### Optional Accessories



**INTJBS**  
Square  
Junction Box



**INTCM**  
Corner/Pole  
Adaptor



**CVCJBB**  
Round  
Junction Box



**PSW4**  
24VAC  
Power Supply



**PSW5**  
12VDC  
Power Supply

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Rev. 11/7/14

