



Optics

- 7 x 5W quad-colour LEDs (RGBA)
- Beam angle: 25°
- 400Hz refresh rate

Control

- DMX channels: 2/3/4 or 7 selectable
- Static colour, colour change, colour fade, auto, sound active and master/slave modes

Dimmer

- 0-100% dimming and variable strobe

Additional features

- Bracket allows for multiple rigging or floor standing applications
- Recessed rear control panel allows panel to sit flat on the floor for uplighting
- 4 push button menu with LED display
- IEC power in/out sockets
- 3-pin XLR in/out sockets

Specifications


- Power consumption: 45W
- Power supply: 100-240V, 50/60Hz
- Dimensions: 202 x 99 x 224mm
- Weight: 2.5kg



Side entry XLR & power connections



Convection cooled, no fan!



Optional IR remote
Order ref: LEDJ90C



Optional Quad Case
Order ref: CASE71

Order ref:	Version
LEDJ59B	Black housing
LEDJ59C	White housing

