



i2267Fw



Cabinet Color	Black & Silver	
Panel	TFT Active Matrix LCD, WLED Backlight, IPS panel 22" Class Widescreen, 16:9 Aspect Ratio 21.5" Viewable Image Size, Diagonal	
Pixel Pitch	0.248mm*0.248mm	
Display Area	476.06mm (H) *267.78mm (V)	
Brightness	250 cd/m2 (typ)	
Contrast Ratio	50,000,000:1 (dynamic)	
Response Time	5ms (typical)	
Viewing Angle	Horizontal: 178 Degrees (CR>10) Vertical: 178 Degrees (CR>10)	
Scanning Frequency	Horizontal: 30K~83KHz Vertical: 55~75 Hz	
Pixel Frequency	148.5MHz	
Maximum Resolution	1920x1080@60Hz	
Recommended Resolution	1920x1080@60Hz	
Supported Resolutions	640x480@60/67/72/75Hz 800x600@56/60/72/75Hz 1024x768@60/70/75Hz 1280x720@60Hz 1440x900@60Hz 1920x1080@60Hz	720x400@70Hz 832x624@75Hz 1280x1024@60/75 Hz 1280x960@60Hz 1680x1050@60Hz
Color	16.7M	
Analog Input	Analog: 0.7Vp-p(standard), 75 OHM, Positive	
Digital Input	DVI-D with HDCP*	
Connectors	Analog RGB Signal: 15-pin D-sub Male Digital Signal: 24-pin DVI-D	
Power Source	Universal 110~240VAC, 50/60Hz	
Power Consumption	On: <45 Watts, Standby: <0.5W	
Plug & Play	DDC/2B, DDC/CI	
User Control	Menu, Up/Volume, Down/ECO, Auto/Source, Power	
OSD Languages	16 Languages including English, French and Spanish	
Regulations	FCC, cCSAus, CE, EPA Energy Star, EPEAT Silver	
Other Features	Ultra Slim, Bezel-less, Detachable Multi-purpose Stand (Standard or Photo Frame type), User Friendly OSD Menu, Includes AOC's e-Saver, Screen+, and iMenu Software	
Dimensions (WxHxD mm)	Monitor: 498x375x121, Carton: 580x389x131	
Dimensions (WxHxD inches)	Monitor: 19.6x14.8x4.8, Carton: 22.8x15.3x5.2	
Weight	3.5 Kg, 6.1 Lbs Net 5.2 Kg, 11.4 Lbs Gross	
Loading Qty w/pallet	20' = 900 pcs.; 40' Std = 1890 pcs.	
UPC Code	685417062188	

Note: Specifications are subject to change without notice. *High-bandwidth Digital Content Protection: Enables viewing of High-Definition contents.
A01/13