

# MINI COAX SERIES CONNECTORS

■ FOR SERIES 23AWG CABLE : SERIES 25AWG CABLE : SERIES 30AWG CABLE

**Holland** offers the most complete line of connectors for mini coax available in the industry. Take advantage of our one piece designs that enable you to terminate your cables in 15 seconds. Our connectors are available for the most popular mini cable sizes ranging from 23-30AWG center conductors. Designed for all applications in CATV, satellite, home theater, broadcast and satellite radio. **Holland's** patented **U Models** (#7,112,093) can be used on a wider range of cable sizes.

## STANDARD COMPRESSION



SLC1855-FP2  
SLC1855-FPU



SLC1855-BNCFP  
SLC1855-BNCFPU



SLC1855-RCAFP  
SLC1855-RCAFPU

## STANDARD CRIMP



F1855-FP



BNC1855-FP



RCA-1855

## RIGHT ANGLE COMPRESSION



SLC1855-90-F



SLC1855-90-BNC



SLC1855-90-RCA

## FEMALE BULKHEADS



GF1855-A



BNCFPFBH



RCAFPFBH

## SATELLITE RADIO



SMBFP



SMBFP90



SMBFPF

## INSTALLERS KIT

Our canvas installer's kits are designed to keep your installation materials organized. Feature six internal pockets to keep connector styles separate, external tool pockets, a retractable handle, wheels, and a 250' internal cable spool.

MODEL #	DESCRIPTION
1855940-STARTER	Kit with Tools, Cable, and Crimp Connectors
1855940STARTERC	Kit with Tools, Cable, and Compression Connectors
INSTALLER PACK	Installation Bag Only. No Tools, Cable, or Connectors



# MINI COAX SERIES CONNECTORS

## SERIES 23AWG CABLE

(Nominal Cable OD .159")

### COMPRESSION CONNECTORS

For Holland HVS Series : **Belden** YR46940, 1855A : **Comscope** 7538 or Similar

MODEL #	DESCRIPTION	PLATING	CLOSURE SIZE
SLC-1855FP2	F Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC-1855-RCAFP	RCA Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC-1855-RCAFPG	RCA Male / Fixed Pin / 1 Piece	Gold	29.8 mm
SLC-1855-BNCFP	BNC Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC90-F-1855	90° F Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC90-RCA-1855	90° RCA Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC90-BNC-1855	90° BNC Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC1855-FPU	90° F Male / Fixed Pin / 1 Piece	Nickel	29.8 mm

## SERIES 23AWG CABLE

(Nominal Cable OD .159")

### CRIMP CONNECTORS

For Holland HVS Series : **Belden** YR46940, 1855A : **Comscope** 7538 or Similar

MODEL #	DESCRIPTION	PLATING	CLOSURE SIZE
F1855-FP	F Male / Fixed Pin / 1 Piece	Nickel	.270 mm
RCA-1855	RCA Male / Fixed Pin / 1 Piece	Nickel	.270 mm
BNC-1855FP	BNC Male / Fixed Pin / 1 Piece	Nickel	.270 mm
GF-1855A	F Female / Fixed Pin / 1 Piece	Nickel	.270 mm
RCAFPFBH	RCA Female / Fixed Pin / 1 Piece	Nickel	.270 mm
BNCFPFBH	BNC Female / Fixed Pin / 1 Piece	Nickel	.270 mm
SMBFP	SMB Plug	Nickel	.213 mm
SMBFP90	90° SMB Plug	Nickel	.213 mm
SMBFPF	SMB Jack	Nickel	.213 mm

## SERIES 25AWG CABLE

(Nominal Cable OD .141")

### COMPRESSION CONNECTORS

For **Belden** 1279R, 1279P, HC2950 or Similar

MODEL #	DESCRIPTION	PLATING	CLOSURE SIZE
SLC-MINI25	F Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC-RCA-MINI25	RCA Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC-BNC-MINI25	BNC Male / Fixed Pin / 1 Piece	Nickel	29.8 mm

## SERIES 30 AWG CABLE

(Nominal Cable OD .110")

### COMPRESSION CONNECTORS

For **Belden** 1790T or Similar

MODEL #	DESCRIPTION	PLATING	CLOSURE SIZE
SLC1790T-FP	F Male / Fixed Pin / 2 Piece	Nickel	29.8 mm
SLC1790T-RCAFP	RCA Male / Fixed Pin / 1 Piece	Nickel	29.8 mm
SLC1790T-BNCFP	BNC Male / Fixed Pin / 1 Piece	Nickel	29.8 mm

**NOTE:** Ask your sales representative for the right connectors if your cable is not listed here.