



Optics

- 1 x 36W tri-colour COB LED
- Beam angle: 60°
- 1100Hz refresh rate

Control

- DMX channels: 3 or 5 selectable
- Static colour, colour change, colour fade, auto run, sound active and master/slave modes

Dimmer

- 0 - 100% dimming with variable strobe

Additional features

- Bracket allows for multiple rigging or floor standing applications
- Recessed rear control panel allows panel to sit flat on the floor for uplighting
- 4 push button menu with LED display
- 3-pin XLR in/out sockets
- IEC Power in/out sockets

Specifications


- Power consumption: 40W
- Power supply: 100-240V~50/60Hz
- Dimensions: 210 x 120 x 220mm
- Weight: 2.1kg



Side entry XLR & power connections



Convection cooled, no fan!



Optional IR remote
Order ref: LEDJ90B



Optional Quad Case
Order ref: CASE95

Order ref:	Version
LEDJ57	Black housing
LEDJ57A	White housing

