

960H Miniature Bullet Camera

CVC637H 3.6mm fixed lens, dark grey housing

CVC637HW 3.6mm fixed lens, white housing

Features

- 700 TV lines of resolution
- Compact and lightweight for discreet installations
- Weather resistant operation
- 5 year warranty

960
H



Specifications

Image Sensor1/3" color 960H CCD
 Resolution.....700 TV lines
 Minimum Illumination.....0.1 lux
 S/N RatioMore than 48dB
 Effective Pixels976 (H) x 494 (V)
 Total Pixels1020 (H) x 508 (V)
 Electronic Shutter1/60 sec – 1/100,000 sec
 Scanning System.....2:1 Interlaced
 Synchronization.....Internal
 Video Output.....1.0Vp-p / 75 ohms
 TV System.....NTSC
 Operating Temperature.....14°F – 122°F
 Power Supply12VDC (power supply not included)
 Power Consumption120mA
 Dimensions.....1.13" (Dia.) x 2.5" (L)
 Weight4 oz.

Optional Accessory



PSW5
12VDC
Power Supply