



AOC Monitors
LED monitor

27" Class, 1920 x 1080

I2721VH

27-inch Ultra Slim IPS Panel with Connectivity You Need

The I2721VH monitor is an ultra-slim 27" class monitor, with an IPS (In-Plane Switching) panel, a superior type of screen that offers consistent image appearance, higher definition, better color accuracy, and greater light transmission from all viewing positions.

Key Features

- 27" viewable image with 16:9 aspect ratio
- VGA, DVI-D, HDMI connectivity
- Slim design with IPS panel
- Full HD Resolution at 1920 x 1080
- VESA 100mm wall mount compliant



AOC

Attractive Ultra-Slim Design

AOC's I2721VH has a sleek, ultra-slim design; black bezel with textured back panel. The screen itself has a matte anti-glare coating that won't leave fingerprints or smudges. The ultra-thin IPS panel allows you to view your spreadsheets or weekend movies from virtually any angle without compromising color uniformity. The buttons are located and laminated on the lower-right bezel for easy access.



Clear Visibility and Vibrant Images

The I2721VH features a 27" display and Full HD 1920 x 1080 resolution, boasting 20,000,000:1 contrast ratio and 5ms response time. The I2721VH provides vibrant images and reveals darker image areas in greater depth, allowing you to watch videos or play games without missing a beat.



User-Friendly and Eco-Friendly Features

The I2721VH comes with VGA, DVI-D, and HDMI connectivity. The VESA 100mm Wall Mount compliant feature allows you to have the monitor mounted on the wall with the appropriate mounting accessory. I2721VH is Energy Star certified with low-power consumption, and comes with AOC's eSaver and iMenu software for both eco-friendly and user-friendly configuration and navigation.

I2721VH Specifications

Cabinet Color	Black
Panel	TFT Active Matrix LCD, LED Backlight, IPS Panel 27" Class Widescreen, 16:9 Aspect Ratio 27" Viewable Image Size, Diagonal
Pixel Pitch	0.311 mm (H)x0.311 mm (V)
Display Area	597.89 mm x 336.31 mm
Brightness	250 cd/m2 (typ)
Contrast Ratio	20,000,000:1 (dynamic)
Response Time	5ms
Viewing Angle	Horizontal: 178 Degrees (CR>10) Vertical: 178 Degrees (CR>10)
Scanning Frequency	Horizontal: 30K~83KHz Vertical: 50~76 Hz
Optimal Resolution Recommended	1920x1080@60Hz 1920x1080@60Hz
Supported Resolutions	640x480@60/67/72/75Hz, 720x400@60Hz, 800x600@56/60/72/75Hz, 832x642@75Hz, 1024x768@60/70/75Hz, 1280x1024@60/75Hz, 1280x720@60Hz, 1280x960@60Hz, 1440x900@60Hz, 1680x1050@60Hz, 1920x1080@60Hz
Color Depth	16.7M colors
Connectors	1 x VGA, 1 x DVI-D, 1 x HDMI
User Control	Source/Auto/Exit, ECO/DCR/+, 4:3/Wide/+, Menu/Enter, Power
Adjustability	Tilt: -5° ~+20°
OSD Languages	16 Languages including English, French and Spanish
Power Source	Universal 110~240VAC, 50/60Hz
Power Consumption	23W (typical), Standby: <0.5W
Regulations	cTUVus, CE, FCC, RoHS, Energy Star®, Windows 8 compatible
Other Features	Direct-Insert Horizontal Connectors, User Friendly Graphical OSD Menu, VESA 100mm Wall Mount Compliant ¹ , Kensington Security Slot, Includes AOC's eSaver Software, i-Menu Software
Dimensions (WxHxD mm)	Monitor: 643.3 x 447.8 x 239.4 Carton: 714 x 508 x 123
Dimensions (WxHxD inches)	Monitor: 25.33 x 17.63 x 9.42 Carton: 28.1 x 20 x 4.84
Weight (Net)	10.35 lbs (4.7 kgs) Net
Weight (Gross)	14.3 lbs (6.5 kgs) Gross
Loading Qty w/pallet	20' = 512 pcs.; 40' Std = 1120 pcs.
UPC Code	685417084883
What's in the Box	27" Monitor, Foot Stand, Power Cord, VGA Cable, Media (Includes drivers, AOC Software, User Manual, Warranty)

*Version subject to change due to updates

1. Webcam function is not available when used as a display. 2. Wall mount arm & bracket not included. Actual product may vary from image shown on datasheet. The information contained herein is subject to change without notice. AOC shall not be liable for technical or editorial errors or omissions contained herein. All other trademarks are property of their respective owners. For more information, visit us.aoc.com or call 888-838-6388