

82-20335

## 2.0Megapixel Vandal-proof IR HD CVI Dome Camera



### Product Features

- High Definition CVI 1080P real-time video
- HD CVI video output ,no delay, lossless, long distance transmission
- Progressive scan CMOS, capture moving object perfectly
- Reach 400 meters coaxial cable real-time transmission
- Support low illumination, auto color to black
- Support ICR switch, realize day& night monitor
- Support 3D noise reduction

### SPEC


|                      |                |
|----------------------|----------------|
| Module               | 82-20335       |
| Image Sensor         | 1/2.9" CMOS    |
| Resolution           | 1920X1080      |
| Image System         | NTSC           |
| Minimum Illumination | 0.lux (LED ON) |
| Lens                 | 2.8-12mm       |
| IR distance          | 20-40m         |

82-20335



|                       |                                    |
|-----------------------|------------------------------------|
| Protection level      | IP66                               |
| Video Output          | BNC×1                              |
| Frame rate            | 30fps (60Hz)                       |
| D&N                   | Support ICR                        |
| SNR                   | >52dB (AGC off)                    |
| Electronic shutter    | 1/60s~1/67500s                     |
| Auto-gain             | Support                            |
| White Balance         | Auto                               |
| Power                 | DC12V (±10%)                       |
| Operation Environment | - 20°C~ 55°C, 10% ~ 90% (humidity) |

### Dimension



### Application

Applicable to the Financial, Telecommunications, Government, schools, airports, factory, Hotels, Museum, Public transit and Other places.