

## 15-U101CT BNC to Terminal Block Converter

### Features:

- BNC plug to Terminal block
- Transmit a full motion mono. Video signal up to 100m, color video signal up to 60m
- Distance up to 600m when used with an active receiver
- No power required

## 15-U101CJ BNC to RJ45 Converter

### Features:

- BNC plug to RJ45 jack
- Transmit a full motion mono. Video signal up to 100m, color video signal up to 60m
- Distance up to 600m when used with an active receiver
- No power required

## 15-U101BT BNC to Terminal Block Video Balun (UTP TX/RX 600M)

### Features:

- BNC plug to Terminal block
- DC to 8MHz bandwidth
- Built-in impedance coupling device and noise filter
- Highly balanced mode of video transmission to immune interference
- Transmit a full motion mono. Video signal up to 600m, color video signal up to 300m
- Distance up to 1.2KM when used with an active receiver
- No power required

## 15-U101BJ BNC to RJ45 Video Balun (UTP TX/RX 600M)

### Features:

- BNC plug to RJ45 jack
- DC to 8MHz bandwidth
- Built-in impedance coupling device and noise filter
- Highly balanced mode of video transmission to immune interference
- Transmit a full motion mono. Video signal up to 600m, color video signal up to 300m
- Distance up to 1.2KM when used with an active receiver
- No power required

### View of Installation:

