

AOC®

e2050Swd



Cabinet Color	Black with Glossy Edges
Panel	TFT Active Matrix LCD, WLED Backlight 20" Class, 16:9 Aspect Ratio 19.5" Viewable Image Size, Diagonal
Pixel Pitch	0.276 x 0.276mm
Display Area	432mm x 240mm
Brightness	200 cd/m2 (typ)
Contrast Ratio	20,000,000:1 (dynamic)
Response Time	5ms (typical)
Viewing Angle	Horizontal: 90 Degrees (CR>10) Vertical: 50 Degrees (CR>10)
Scanning Frequency	Horizontal: 30KHz~83KHz Vertical: 50Hz~76 Hz
Pixel Frequency	140MHz
Maximum Resolution	1600x900@60Hz
Recommended Resolution	1600x900@60Hz
Supported Resolutions	640x480 @60Hz/67Hz/72Hz/75Hz 720x400 @70Hz 800x600 @56Hz /60Hz/72Hz/75Hz 832x624 @75Hz 1024x768@60Hz/70Hz/75Hz 1280x1024@60Hz/75Hz 1600x900 @60Hz
Color	16.7M
Signal Input	Analog: 0.7Vp-p(standard), 75 OHM, Positive
Digital Input	DVI-D with HDCP*
Connectors	Analog RGB Signal: 15-pin D-sub Male
Power Source	Universal 110~240VAC, 50/60Hz
Power Consumption	On: <17 Watts, Standby: <0.5W
Plug & Play	VESA DDC2B/CI
User Control	Auto/Exit, Left/Eco(DCR), Right/4:3, Menu/Enter, Power
OSD Languages	16 Languages including English, French and Spanish
Regulations	cCSAus, FCC, TUV/S, ROHS, EPA 5.1, EPEAT Silver
Other Features	User Friendly Graphical OSD Menu, VESA 75 mm Wall Mount Compliant*, Kensington Security Slot, Direct-Insert Horizontal Connectors
Dimensions (WxHxD mm)	Monitor: 361x478x175, Carton: 528x376x108mm
Dimensions (WxHxD inches)	Monitor: 14.2x18.8x6.7, Carton: 20.8x14.8x4.3
Weight	2.8Kg, 6.2Lbs Net 4.0 Kg, 8.8Lbs Gross
Loading Qty w/pallet	20' = 1220 pcs.; 40' Std = 2440 pcs.
UPC Code	685417056187

Note: Specifications are subject to change without notice. *Wall mount arm & bracket not included.

A10/12