

82-20305

3MP EXIR Bullet Network Camera



EXIR



Key features

- 3.0 megapixel (2048 x 1536) resolution
- Full HD1080p real-time video
- DWDR & 3D DNR & BLC
- EXIR illuminators: up to 50m
- IP66
- PoE

Dimensions



Unit: mm

82-20305	
Camera	
Image sensor	1/3" progressive scan CMOS
Min. illumination	0.19lux@F2.0, AGC on 0 lux with IR
Shutter time	1/25s (1/30s) ~ 1/100,000s
Lens	4mm@ F2.0 angle of view: 75.8
Lens mount	M12
Day & night	ICR
Digital noise reduction	3D DNR
Wide dynamic range	Digital WDR
Backlight compensation	Yes, zone configurable
Compression standard	
Video compression	H.264 / MJPEG
H.264 compression profile	Main profile
Bit rate	32 Kbps ~ 16 Mbps
Dual stream	Yes
Image	
Max. image resolution	2048 x 1536
Frame rate	60Hz: 15fps (2048 x 1536), 30fps (1920 x 1080), 30fps (1280 x 720)
Image settings	Saturation, brightness, contrast adjustable through client software or web browser
Network	
Network storage	NAS
Alarm trigger	Motion detection, tampering alarm
Protocols	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP, RTSP, PPPoE, SMTP, NTP, SNMP, HTTPS, FTP, 802.1X, Qos
System compatibility	ONVIF, PSIA, CGI
General functionalities	User authentication, watermark
Interface	
Communication interface	1 RJ45 10M / 100M ethernet port
General	
Operating conditions	-30°C ~ 60°C (-22°F ~ 140°F) humidity 95% or less (non-condensing)
Power supply	12 VDC ± 10%, PoE (802.3af)
Power consumption	Max. 7W (9W with ICR on)
Ingress protection	IP66
EXIR range	up to 50m
Dimensions	100.5 x 88.1 x 157.3 mm
Weight	700g (1.5 lbs)