




# LEDSTRIPS


CHLS24X



CHLS23X



CHLS7X



CHLS15X




CHLS13X



CHLS16RGBW




CHLS18WWWC



CHLS19X



CHLS20X




CHLS21X




CHLS11X



CHLS22X



CHLS9X




CHLS17RGB/2



CHLS14



CHLS27X



CHLS26X



IP	Langte	Breedte	Type	Aantal Leids	LED's/m	Afmeting per	Aantal LED's	Coating	Lijn Spanning	Verbruik	Verbruik/W	Stroom	Stroom/W	Ref.	Kleur	Pris	
IP61	5m	10mm	type 5050	150	30/m	3 LED 10cm	33mm	Epoxy	√	12v	19.5W	3.9W	1.6A	0.32A	CHLS24W	wit	●
											20.5W	4.1W	1.7A	0.34A	CHLS24WW	warm wit	●
											29.5W	5.9W	2.5A	0.5A	CHLS24RGB	RGB	●●●
											19.5W	3.9W	1.6A	0.36A	CHLS24B	blauw	●
											20.5W	4.1W	1.7A	0.34A	CHLS24G	groen	●
											25W	5W	2.1A	0.42A	CHLS24R	rood	●
IP61	5m	10mm	type 3528	300	60/m	3 LED 5cm	16.5mm	Epoxy	√	12V	18W	3.6W	1.5A	0.3A	CHLS23W	wit	●
											17W	3.4W	1.4A	0.28A	CHLS23B	blauw	●
											20.5W	4.1W	1.7A	0.34A	CHLS23G	groen	●
											19.5W	3.9W	1.6A	0.32A	CHLS23R	rood	●
											19.5W	3.9W	1.6A	0.32A	CHLS23Y	geel/amber	●
											19.5W	3.9W	1.6A	0.32A	CHLS23W	warm wit	●
IP61	5m	10mm	type 5050	300	60/m	6 LED 10cm	16.5mm	Epoxy	√	24V	53W	10.6W	2.1A	0.42A	CHLS7W	wit	●
								-							CHLS7W/C	wit	●
								Epoxy							CHLS7NW	Daglicht	●
								-							CHLS7NW/C	Daglicht	●
								Epoxy							CHLS7WW	warm wit	●
								-							CHLS7WW/C	warm wit	●
								Epoxy							CHLS7RGB	RGB	●●●
								-							CHLS7RGB/C	RGB	●●●
Epoxy	CHLS7B	blauw	●														
IP61	5m	10mm	type 5050	300	60/m	3 LED 5cm	16.5mm	Epoxy	√	12V	53W	10.6W	4.2A	0.84A	CHLS15W	wit	●
											43W	8.6W	3.3A	0.66A	CHLS15RGB	RGB	●●●
											53W	10.6W	4.2A	0.84A	CHLS15NW	Daglicht	●
IP61	5m	10mm	type 3528	600	120/m	6 LED 5cm	8.3mm	Epoxy	√	24V	40W	8W	1.7A	0.34A	CHLS13W	wit	●
											39W	7.8W	1.6A	0.32A	CHLS13WWW	wit & warm wit	●
											39W	7.8W	1.6A	0.32A	CHLS13B	blauw	●
IP61	5m	12mm	type 5050+3528	2x150	30/m	6 LED 10cm	16.5mm	Epoxy	√	12V	48W	9.6W	4A	0.8A	CHLS16RGBW	RGB-wit	●●●●
											36W	2x 3.6W	3A	0.34A	CHLS18WWWC	wit&warm wit	●●
IP51	5m	10mm	type 3528	1200	240/m	6 LED 2.5cm	4.2mm	-	√	24V	100W	20W	4.2A	0.84A	CHLS19W	wit	●
											100W	20W	4.2A	0.84A	CHLS19WW	warm wit	●
IP61	5m	15mm	type 3528	1200	240/m	12 LED 5cm	8.4mm	Epoxy	√	24V	70W	14W	2.9A	0.58A	CHLS20W	wit	●
											70W	14W	2.9A	0.58A	CHLS20WW	warm wit	●
IP51	5m	24mm	type 3528	900	180/m	9 LED 5cm	16.5mm	Epoxy	√	12V	40W	8W	3.3A	0.66A	CHLS21W	wit	●
											37W	7.4A	3.1A	0.62A	CHLS21WW	warm wit	●
IP68	5m	12mm	type 5050	150	30/m	3 LED 10cm	33mm	silicone	√	12V	19.5W	3.9W	1.6A	0.32A	CHLS11WNG	wit	●
											20.5W	4.1W	1.7A	0.34A	CHLS11WW	warm wit	●
											19.5W	3.9W	1.6A	0.32A	CHLS11WNG	warm wit	●
IP68	5m	12mm	type 5050	300	60/m	3 LED 5cm	16.5mm	PVC	-	12V	40W	8W	3.3A	0.66A	CHLS11BNG	blauw	●
											40W	8W	3.3A	0.66A	CHLS22W	wit	●
											40W	8W	3.3A	0.66A	CHLS22WW	warm wit	●
IP68	5m	8mm	type 335	300	60/m	3 LED 5cm	16.5mm	silicone	√	12V	22W	4.4W	1.8A	0.36A	CHLS22RGB	RGB	●●●
											22W	4.4W	1.8A	0.36A	CHLS9W	wit	●
											22W	4.4W	1.8A	0.36A	CHLS9WW	warm wit	●
IP61	2m	10mm	type 5050	60	30/m	3 LED 10cm	33mm	Epoxy	√	12V	12.5W	6.25W	1.1A	0.550A	CHLS17RGB/2	RGB	●●●
											12.5W	6.25W	1.1A	0.550A	CHLS17RGB/2	RGB	●●●
IP61	5m	16mm	type 5050	270	54/m	non	non	Epoxy	√	12V	45W	9W	4A	0.8A	CHLS14	RGB	●●●
											45W	9W	4A	0.8A	CHLS14	RGB	●●●
IP68	5m	12mm	type 5050	150	30/m	3 LED 10cm	33mm	PVC	-	12V	20W	4W	1.6A	0.32A	CHLS27W	wit	●
											25A	0.5A	CHLS27WW	warm wit	●		
IP68	5m	12mm	type 5050	300	60/m	6 LED 10cm	16.5mm	PVC	-	24V	40w	8W	1.7A	0.34A	CHLS27RGB	RGB	●●●
											1.8A	0.36A	CHLS26W	wit	●		
IP68	5m	12mm	type 5050	300	60/m	6 LED 10cm	16.5mm	PVC	-	24V	40w	8W	1.7A	0.34A	CHLS26WW	warm wit	●
											1.8A	0.36A	CHLS26RGB	RGB	●●●		



IP	Longueur	Largeur	Type	Nbr de LEDs	LED/m	Scalabilité	Distance LEDs	Revêtement	Colonne	Voltage	Consommation	Consommation/M	Courant	Courant/M	Ref.	Couleur	Prix
IP61	5m	10mm	type 5050	150	30/m	3 LED 10cm	33mm	Epoxy	√	12v	19.5W	3.9W	1.6A	0.32A	CHLS24W	blanc	●
											20.5W	4.1W	1.7A	0.34A	CHLS24WW	blanc chaud	●
											29.5W	5.9W	2.5A	0.5A	CHLS24RGB	RVB	●●●
											19.5W	3.9W	1.6A	0.36A	CHLS24B	bleu	●
											20.5W	4.1W	1.7A	0.34A	CHLS24G	vert	●
											25W	5W	2.1A	0.42A	CHLS24R	rouge	●
IP61	5m	10mm	type 3528	300	60/m	3 LED 5cm	16.5mm	Epoxy	√	12V	18W	3.6W	1.5A	0.3A	CHLS23W	blanc	●
											17W	3.4W	1.4A	0.28A	CHLS23B	bleu	●
											20.5W	4.1W	1.7A	0.34A	CHLS23G	vert	●
											19.5W	3.9W	1.6A	0.32A	CHLS23R	rouge	●
															CHLS23Y	jaune/ambéré	●
															CHLS23WW	blanc chaud	●
IP61	5m	10mm	type 5050	300	60/m	6 LED 10cm	16.5mm	Epoxy	√	24V	53W	10.6W	2.1A	0.42A	CHLS7W	blanc	●
-								CHLS7W/C							blanc	●	
Epoxy								CHLS7NW							lumière du jour	●	
-								CHLS7NW/C							lumière du jour	●	
Epoxy								CHLS7WW							blanc chaud	●	
-								CHLS7WW/C							blanc chaud	●	
Epoxy								CHLS7RGB							RVB	●●●	
-								CHLS7RGB/C							RVB	●●●	
IP61	5m	10mm	type 5050	300	60/m	3 LED 5cm	16.5mm	Epoxy	√	12V	53W	10.6W	4.2A	0.84A	CHLS15W	blanc	●
-								CHLS15NW			lumière du jour	●					
-								CHLS15WW			blanc chaud	●					
-								CHLS15RGB			RVB	●●●					
-								CHLS13W			blanc	●					
-								CHLS13WW			blanc chaud	●					
IP61	5m	10mm	type 3528	600	120/m	6 LED 5cm	8.3mm	Epoxy	√	24V	40W	8W	1.7A	0.34A	CHLS13W	blanc	●
											39W	7.8W	1.6A	0.32A	CHLS13B	bleu	●
															CHLS13WWW	blanc & blanc chaud	●
IP61	5m	12mm	type 5050-3528	2x150	30/m	6 LED 10cm	16.5mm	Epoxy	√	12V	48W	9.6W	4A	0.8A	CHLS16RGBW	RVB-blanc	●●●●
IP61	5m	10mm	type 3528	2x300	120/m	6 LED 5cm	8.3mm	Epoxy	√	12V	36W	2x 3.6W	3A	0.34A	CHLS18WWWC	blanc & blanc chaud	●●
IP51	5m	10mm	type 3528	1200	240/m	6 LED 2.5cm	4.2mm	-	√	24V	100W	20W	4.2A	0.84A	CHLS19W	blanc	●
															CHLS19WW	blanc chaud	●
IP61	5m	15mm	type 3528	1200	240/m	12 LED 5cm	8.4mm	Epoxy	√	24V	70W	14W	2.9A	0.58A	CHLS20W	blanc	●
															CHLS20WW	blanc chaud	●
IP51	5m	24mm	type 3528	900	180/m	9 LED 5cm	16.5mm	Epoxy	√	12V	40W	8W	3.3A	0.66A	CHLS21W	blanc	●
											37W	7.4A	3.1A	0.62A	CHLS21WW	blanc chaud	●
IP68	5m	12mm	type 5050	150	30/m	3 LED 10cm	33mm	silicone	√	12V	19.5W	3.9W	1.6A	0.32A	CHLS11WNG	blanc	●
											20.5W	4.1W	1.7A	0.34A	CHLS11WW	blanc chaud	●
											19.5W	3.9W	1.6A	0.32A	CHLS11WNGG	blanc chaud	●
IP68	5m	12mm	type 5050	300	60/m	3 LED 5cm	16.5mm	PVC	-	12V	40W	8W	3.3A	0.66A	CHLS22W	blanc	●
															CHLS22WW	blanc chaud	●
															CHLS22RGB	RVB	●●●
IP68	5m	8mm	type 335	300	60/m	3 LED 5cm	16.5mm	silicone	√	12V	22W	4.4W	1.8A	0.36A	CHLS9W	blanc	●
															CHLS9WW	blanc chaud	●
															CHLS9WWNG	blanc chaud	●
IP61	2m	10mm	type 5050	60	30/m	3 LED 10cm	33mm	Epoxy	√	12V	12.5W	6.25W	1.1A	0.550A	CHLS17RGB/2	RVB	●●●
IP61	5M	16mm	type 5050	270	54/m	non	non	Epoxy	√	12V	45W	9W	4A	0.8A	CHLS14	RVB	●●●
IP68	5m	12mm	type 5050	150	30/m	3 LED 10cm	33mm	PVC	-	12V	20W	4W	1.6A	0.32A	CHLS27W	blanc	●
													2.5A	0.5A	CHLS27WW	blanc chaud	●
IP68	5m	12mm	type 5050	300	60/m	6 LED 10cm	16.5mm	PVC	-	24V	40w	8W	1.7A	0.34A	CHLS26W	blanc	●
													1.8A	0.36A	CHLS26WW	blanc chaud	●
														CHLS26RGB	RVB	●●●	