

Lenovo
Colour: Black
DisplayPort: Yes
Energy Star: Yes
Environmentally Friendly: Yes
Form Factor: Small Form Factor
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: ThinkCentre M700
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Number of USB Ports: 6
Total Solid State Drive Capacity: 128 GB
VGA: Yes
Wireless LAN: No

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM

General Information

Brand Name: Lenovo
Manufacturer Part Number: 10GT0059UK
Manufacturer Website Address: <http://www.lenovo.com/uk/en/>
Manufacturer: Lenovo Group Limited
Product Line: ThinkCentre
Product Model: 10GT0059UK
Product Name: ThinkCentre M700 10GT0059UK Desktop Computer
Product Series: M700
Product Type: Desktop Computer

Interfaces/Ports

DisplayPort: Yes
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 4
Total Number of USB Ports: 6
VGA: Yes

Memory

Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Energy Star: Yes
Environmental Certification: GREENGUARD
Environmentally Friendly: Yes
Features: Security Slot
Package Contents:

- ThinkCentre M700 10GT0059UK Desktop Computer
- Keyboard
- Mouse

Network & Communication

Wireless LAN: No

Physical Characteristics

Colour: Black
Depth: 356.9 mm
Form Factor: Small Form Factor
Height: 87.9 mm
Weight (Approximate): 5.58 kg
Width: 338.1 mm

Processor & Chipset

Processor Generation: 6th Gen
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3

Software

Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro

Storage

Optical Drive Type: DVD-Writer
Optical Media Supported: DVD-RAM/±R/±RW
Total Solid State Drive Capacity: 128 GB

Warranty

Limited Warranty: 3 Year