

## Basic

Brand Name:	HP
DisplayPort:	Yes
Form Factor:	Small Form Factor
Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Number of DisplayPort Outputs:	1
Number of USB 2.0 Ports:	4
Number of USB 3.1 Ports:	4
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3
Product Family:	Business Desktop ProDesk 400 G
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Number of USB Ports:	8
Total Solid State Drive Capacity:	128 GB
VGA:	Yes

## Display & Graphics

Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM

## General Information

Brand Name:	HP
Manufacturer Part Number:	1KP53EA#ABU
Manufacturer Website Address:	<a href="http://www.hp.com">http://www.hp.com</a>
Manufacturer:	HP Inc.
Product Line:	Business Desktop
Product Name:	ProDesk 400 G4 Small Form Factor PC
Product Series:	ProDesk 400 G4
Product Type:	Desktop Computer

## Interfaces/Ports

DisplayPort:	Yes
Number of DisplayPort Outputs:	1
Number of USB 2.0 Ports:	4
Number of USB 3.1 Ports:	4
Total Number of USB Ports:	8
VGA:	Yes

## Memory

Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Features:	Security Slot
-----------	---------------

## Physical Characteristics

Depth:	297.2 mm
Form Factor:	Small Form Factor
Height:	94 mm
Weight (Approximate):	4.60 kg
Width:	269.2 mm

## Power Description

Input Voltage:	120 V AC
----------------	----------

## Processor & Chipset

Processor Generation:	6th Gen
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3

## Storage

Total Solid State Drive Capacity:	128 GB
-----------------------------------	--------