

M2470SWH

59.9 cmcm (23.6 inch") LCD MONITOR

This 23.6-inch WLED display is designed for fast-paced fun and entertainment, plus offers impressive performance for all your home computing needs. The MVA panel delivers extra-wide 178 degree viewing angles. With high contrast ratios and Full HD resolution, you'll also enjoy excellent picture quality.



AUDIO



HDMI



HEADPHONE OUT



TILT

GENERAL FEATURES

Line	Value-line
Panel Type	MVA
Panel Size	23.6 inch" / 59.9 cm cm
Aspect Ratio	16:9
Brightness	250 nits cd/m ²
Contrast Ratio Dynamic	50M:1
Contrast Ratio Static	3000:1
Pixel Pitch(H) (V)	0.2715
Display Area (H x V)	521.28x293.32 mm
Viewing Angle (CR >= 10)	178/178 °
Response time	5 msms GTG
Color	Black

SCANNING FREQUENCY

Scanning Frequency	30-83khz/50-76hz
Pixel Frequency	165 MHz

RESOLUTION

Maximum Resolution	1920x1080@60Hz
Recommended Resolution	1920x1080@60Hz
Colors	16.7 Million
HDCP compatible	Yes

CONNECTORS

D-Sub	Yes
DVI	-
HDMI	2x
USB	-
MHL	-
DisplayPort	-

POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 17.96W, Standby: 0.37W, Off: 0.19W

Zero Power Switch	-
-------------------	---

OTHER FEATURES

MVA Panel	Yes
Speakers	Yes
Speakers icon	https://aoc-pim.s3.amazonaws.com/
Vesa Wallmount	100x100
Speakers	WattW

Regulations	Energystar 6 TCO 6 TUV-GS TUV-Bauart CE FCC EAC PVC/BRF Free ISO Certified Production RoHS compliant EUP compliant Reach compliant dicom_part_14
-------------	--

ACCESSORIES

VGA Cable
HDMI Cable
Power Schuko C7 Cable

ERGONOMIC DATA

Pivot	No
Tilt	-5/25

DIMENSIONS

Product with stand (W×H×D)	551.4x400.4x221 mm
----------------------------	--------------------

Packaging (W×H×D)	620x435x127 mm
Weight	3.58 kg wo/packaging 5.21 kg w/packaging

Warranty	3 Years
EAN	4038986144995