

G2260VWQ6

54.6 cmcm (21.5 inch") LCD MONITOR

Featuring AMD FreeSync™ technology to eliminate tearing, stuttering and input lag, the 21.5-inch AOC G2260VWQ6 also boasts a 1ms response time and the innovative Anti-Blue Light technology, which reduces eye fatigue for a more comfortable viewing.



HDMI



HEADPHONE OUT



DISPLAYPORT



TILT

GENERAL FEATURES

Line	AOC Gaming
Panel Type	TN
Panel Size	21.5 inch" / 54.6 cm cm
Aspect Ratio	16:9
Brightness	250 nits cd/m ²
Contrast Ratio Dynamic	20M:1
Contrast Ratio Static	1000:1
Pixel Pitch(H) (V)	0.248
Display Area (H x V)	477.5x268.5 mm
Viewing Angle (CR >= 10)	170/160 °
Response time	1 msms
Color	Black

SCANNING FREQUENCY

Scanning Frequency	30-83khz/48-76Hz
Pixel Frequency	148.5MHZ

RESOLUTION

Maximum Resolution	1920x1080@75Hz
Recommended Resolution	1920x1080@75Hz
Colors	16.7 Million
HDCP compatible	Yes

CONNECTORS

D-Sub	Yes
DVI	-
HDMI	1x
USB	-
MHL	-
DisplayPort	1

POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 20W, Standby: 0.5W, Off: 0.3W
Zero Power Switch	-

OTHER FEATURES

144hz icon	https://aoc-pim.s3.amazonaws.com/
1 MS	Yes
1MS Icon	https://aoc-pim.s3.amazonaws.com/
Adaptive-Sync	Yes
FreeSync Icon	https://aoc-pim.s3.amazonaws.com/
Speakers	-
Speakers icon	https://aoc-pim.s3.amazonaws.com/

Regulations

Energystar 6
TCO 6
TUV-GS
TUV-Bauart
CE
FCC
EAC
PVC/BRF Free
ISO Certified Production
RoHS compliant
EUP compliant
Reach compliant
dicom_part_14

ACCESSORIES

VGA Cable
HDMI Cable
Displayport Cable
Power Schuko C7 Cable

ERGONOMIC DATA

Pivot	No
Tilt	-5/+20

DIMENSIONS

Product with stand (W×H×D)	511.8x376.9x184.4 mm
Packaging (W×H×D)	693x127x435 mm
Weight	3.03 kg wo/packaging 4.15 kg w/packaging
Warranty	3 Years
EAN	4038986125314