

I2080SW

49.4 cmcm (19.5 inch") LCD MONITOR

The versatile 19.5-inch AOC I2080SW delivers reliable performance for all your home computing needs. An IPS panel and 5ms response time ensure clear, detailed imagery and wide viewing angles, even for games and movies. With an integrated VESA mount, you also have the option to hang this display on the wall.



TILT

GENERAL FEATURES

Line	Value-line
Panel Type	IPS
Panel Size	19.5 inch" / 49.4 cm cm
Aspect Ratio	16:9
Brightness	250 nits cd/m ²
Contrast Ratio Dynamic	20M:1
Contrast Ratio Static	1000:1
Pixel Pitch(H) (V)	0.2907
Display Area (H x V)	418.61 x 262.35 mm mm
Viewing Angle (CR >= 10)	178/178 °
Response time	5 msms GTG
Color	Black

SCANNING FREQUENCY

Scanning Frequency	30 -83 kHz (H) / 50 -76 Hz (V)
--------------------	--------------------------------

Pixel Frequency

RESOLUTION

Maximum Resolution	
Recommended Resolution	1440x900@60Hz
Colors	16.7 Million
HDCP compatible	-

CONNECTORS

D-Sub	Yes
DVI	-
HDMI	-
USB	-
MHL	-
DisplayPort	-

POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 19W, Standby: 0.5W, Off: 0.3W
Zero Power Switch	-

OTHER FEATURES

IPS panel	Yes
IPS Icon	https://aoc-pim.s3.amazonaws.com/
Plug and play	Yes
Kensington Lock	Yes
i-Menu	Yes
Vesa Wallmount	100x100

Regulations	Energystar 6 TCO no EPEAT Silver TUV-GS TUV-Bauart CE FCC EAC PVC/BRF Free ISO Certified Production RoHS compliant EUP compliant Reach compliant dicom_part_14
-------------	---

ACCESSORIES

VGA Cable
Power Schuko C5 Cable

ERGONOMIC DATA

Pivot	No
Swivel	
Tilt	-5°~23°

DIMENSIONS

Product with stand (W×H×D)	375x454.6x190 mm
----------------------------	------------------

Packaging (W×H×D)	546x111x368 mm
Weight	2.14 kg wo/packaging 3.15 kg w/packaging

Warranty	3 Years
EAN	4038986105293