


STANDARD ON/OFF MICROWAVE SENSOR

- Adjustable microwave sensor: with options to adjust 2-50 lux or disable, detection range 10-100% and time 5 secs - 15 mins
- The microwave sensor is discreetly placed behind the diffuser: making it unobtrusive so there is no compromise to the appearance of the fitting or the room design



LED OVAL BULKHEAD FITTINGS

- Polycarbonate & ABS construction
- Ceiling or wall mounted
- Polycarbonate opal diffuser
- M.O.M: 1 / O.P.Q: 10

Code	Version	Colour	Wattage	Colour Temp.	Luminaire Lumens	Avg. Rated Life (Hrs)	IP Rating	Energy Rating
LEDOVAL	Standard	Black	13W	4200K	1100 lm	35,000 hrs	IP54	A+
LEDOVALMW	MW Sensor							

Eterna
LED
2 YEAR
Warranty
Subject to T&C's



Eterna LEDOVAL/MW

This luminaire contains built-in LED lamps.

A++
A+
A
B
C
D
E

} LED

The lamps cannot be changed in the luminaire.

874/2012

LED LAMP SPECIFICATIONS:

Luminaire lumens (with diffuser)	1100 lm
Lumens from chip (no diffuser)	1300 lm
Useful lumens	1050 lm
Rated Wattage	13W
Rated luminous flux	1050 lm
Nominal life time of the lamp	35,000 hrs
Colour temperature	4200K
Number of switching cycles before premature lamp failure	>15,000
Warm-up time up to 60% of the full light output	Instant full light
Dimmable	No
Nominal beam angle	120°
Rated power	13W
Rated lamp lifetime	35,000 hrs
Lamp power factor	>0.85
Lumen maintenance factor at end of nominal life	>0.7
Starting time	<0.1s
Colour rendering	>80
Colour consistency	Within a six step Macadam ellipse
Rated peak intensity	450cd
Rated beam angle	120°
Voltage / Frequency	240V~50Hz

Not suitable for accent lighting