



Main

Range of product	Mureva BOX
Product or component type	Junction box
Colour tint	Grey RAL 7035
Quantity per set	5 pieces

Complementary

Wiring device mounting	Surface
Cable entry	Grommets
Fixing mode	Clip-on cover
Base dimension	80 x 80 x 45 mm
Cable entry number	7 grommets Ø 20 mm
Material	ABS (acrylonitrile butadiene-styrene) body PP (polypropylene) cover SBS (styrene butadiene styrene) grommet
Electrical insulation class	Class II according to IEC 536
Height	51 mm
Width	98 mm
Depth	98 mm
Product weight	0.08 kg

Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP55 according to IEC 60529
IK degree of protection	IK07 according to EN 50102
Fire resistance	650 °C
Standards	EN 60670
Product certifications	CE

Environmental characteristic	Halogen free
------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------