



### Main

Range of product	Mureva BOX
Product or component type	Junction box
Colour tint	Grey RAL 7035
Quantity per set	5 pieces

### Complementary

Wiring device mounting	Surface
Cable entry	Grommets
Fixing mode	Screw-fixed cover
Base dimension	105 x 105 x 55 mm
Cable entry number	7 grommets Ø 25 mm
Material	PP (polypropylene) cover SBS (styrene butadiene styrene) grommet
Electrical insulation class	Class II according to IEC 536
Height	61 mm
Width	125 mm
Depth	125 mm
Product weight	0.18 kg

### Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP55 according to IEC 60529
IK degree of protection	IK07 according to EN 50102
Fire resistance	750 °C
Standards	EN 60670
Product certifications	CE
Environmental characteristic	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------