



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Rated power in W	50 W
Input voltage	110...250 V AC 50/60 Hz
Electrical connection	4 screw terminals 2.5 mm <sup>2</sup>

### Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	VDE UL
Material	Extruded aluminium for body Plastic for cover
Height	External : 110 mm
Width	External : 60 mm
Depth	External : 90 mm
Condition of use	Heaters must be installed with a thermal controller Electrical protection is needed Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity

 Schneider Electric declaration of conformity

---

REACH

Reference not containing SVHC above the threshold  
Reference not containing SVHC above the threshold

---

**Contractual warranty**

---

Warranty period

18 months

---