



### Main

Range of product	Harmony XAC
Product or component type	Head for push-button
Component name	XACA

### Complementary

Marking	Unmarked
Operator additional information	Booted
Cap/Operator or lens colour	White
Product compatibility	XACA..
Mounting location	Front of enclosure
Sale per indivisible quantity	10
Standards	EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14 EN/IEC 60204-32
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn 10...500 Hz IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Overvoltage category	Class II IEC 61140
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK08 EN 50102
Product weight	0.01 kg

### Contractual warranty

Warranty period	18 months
-----------------	-----------