



Overview

Model Name	Rack PDU, Switched, 1U, 16A, 208/230V, (8)C13
Includes	Installation guide , Rack Mounting brackets , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , <![CDATA[Cote D'Ivoire]]> , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guatemala , Guinea , Guyana , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Mauritania , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Output

Nominal Output Voltage	208V , 230V
Maximum Total Current Draw per Phase	16 A
Output Connections	(8) IEC 320 C13 (Battery Backup)
Always on Outlets	0

Input

Nominal Input Voltage	200V , 208V , 230V
-----------------------	--------------------

Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	16 A
Input Connections	IEC-320 C20
Cord Length	2.5 meters
Number of Power Cords	1
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	0 A
Maximum Input Current per phase	20 A
Load Capacity	3680 VA

Physical

Net Weight	2.27 kg
Maximum Height	44.0 mm
Maximum Width	445.0 mm
Maximum Depth	108.0 mm
Shipping Weight	3.45 kg
Shipping Height	70.0 mm
Shipping Width	486.0 mm
Shipping Depth	343.0 mm
Color	Black

Environmental

Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	CE , CSA , EN 55022 Class A , EN 55024 , EN 61000-3-2 , EN 61000-3-3 , GOST , IRAM , MIC , UL 60950 , UL Listed , VCCI , VDE , cUL Listed
Standard warranty	2 years repair or replace