



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Rated power in W	90 W
Input voltage	120 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

### Complementary

Operating position	Vertical Horizontal
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	External : 280 mm
Width	External : 450 mm
Depth	External : 1.6 mm
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing mode	By 4 screws
Mounting support	Standard mounting plate DIN rail Adhesive Velcro Telequick mounting plate

**Offer Sustainability**

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------