



Main

| | |
|------------------------------------|----------------------|
| Accessory / separate part category | Cabling accessory |
| Accessory / separate part type | Pre-wired connectors |
| Series name | Application |

Complementary

| | |
|--------------------------------|---|
| Electrical connection | Straight female connector, connector type: M12 8 pins |
| Cable connector fixing | Screw-on |
| Collar material | Stainless steel 316L |
| Status LED | Without |
| Cable length | 5 m |
| Cable outer diameter | 5.2 mm |
| Cable composition | 8 x 0.25 mm ² |
| Wire insulation material | PUR |
| [Ue] rated operational voltage | 30 V AC 36 V DC |
| [In] rated current | 2 A |
| Contact resistance | <= 5000 μOhm |
| Insulating resistance | >= 1 GΩ |

Environment

| | |
|---------------------------------------|--|
| IP degree of protection | IP67 |
| Product certifications | CULus |
| Ambient air temperature for operation | -35...90 °C (static) -5...90 °C (flexing) |
| Ambient air temperature for storage | -35...100 °C |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Not Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0649 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Connections and Schemes

Connectors



- GY : Grey
- PK : Pink
- BU : Blue
- WH : White
- RD : Red
- BN : Brown
- GN : Green
- YE : Yellow