



### Main

Range of product	Harmony 9001K
Product or component type	Complete push-button
Device short name	K
Operator profile	Black flush
Operator additional information	Full guard in plastic

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Light source	Without
Light block supply	Without supply
[Ie] rated operational current	10 A (AC-15) 10 A (DC-13)
Contacts operation	Standard

### Environment

Product certifications	NEMA UL listed file E42259 CCN NKCR CE CSA LR 25490 class 3211 03
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>