

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638017200](#)
Status: **Active**
Description: TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10AWG

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	T9999
Application Tooling Video	www.youtube.com/watch?v=1Gj31xD5L_c , www.youtube.com/watch?v=lj0kZ20_wTo , www.youtube.com/watch?v=0avd9Rlph58 , www.youtube.com/watch?v=LjjqR9hEuNk
Comments	2.0 Ton Press, 30mm press stroke
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Product Name	TM-3000™
Tool Type	Bench Press
UPC	822350060769
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number TM3000

Reference - Drawing Numbers

Application Tooling Documents
 ATS-640162595, TM-638000029, TM-638000029CN, TM-638000029DE, TM-638000029FR, TM-638000029IT, TM-638000029JP, TM-638000029KR, TM-638000029MY, TM-638000029PL, TM-638000029RU, TM-638000029SK, TM-638000029SP, TM-638000029TH, TM-638000029TW, TM-638000029VN, TM-638017299, TM-638017299CH, TM-638017299DE, TM-638017299FR, TM-638017299IT, TM-638017299JP, TM-638017299KR, TM-638017299MA, TM-638017299PL, TM-638017299RU, TM-638017299SK, TM-638017299SP, TM-638017299TH, TM-638017299TW, TM-638017299VN, TM-640160065, TM-640160065CN, TM-640160065DE, TM-640160065FR, TM-640160065IT, TM-640160065JP, TM-640160065KR, TM-640160065MY,



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[T9999 Series](#)

Use With

Molex FineAdjust and Mini-Mac Applicators plus the Molex Tape Crimp Module [64016-2000](#) and most industry standard applicators.

TM-640160065PL, TM-640160065RU,
TM-640160065SK, TM-640160065SP,
TM-640160065TH, TM-640160065TW,
TM-640160065VN, TM-640162000, TM-640162000SP

This document was generated on 05/24/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION